CHALFANT

Manufacturing Company

INDEX

Intro pg 2-9

Trays pg 10-11

Connectors pg 12-13

Mounting pg 14-19

Accessories pg 20-22

Barrier Strips pg 23-24

Underfloor pg 25

Installation Instructions pg 26-41

Chalfant WM PG Rev 15-1

www.chalfantcabletray.com
(330) 273-3510



CHALFANT
Manufacturing Company

Why Choose Wire Mesh Cable Tray?

Wire Mesh Cable Tray has quickly become the industry's favored means of wire management. Its versatility and light weight make it a perfect solution for a wide variety of applications. Along with this light weight comes the ability to span great lengths with strength and security as well as easily configuring to navigate around corners, up and down sloped surfaces and even level changes.

Why Look to Chalfant?

Chalfant is among the most trusted names in cable management. With over 70 years of outstanding service our success can be traced to providing quality cable tray that meets your needs on time and within budget. From production to distribution, our sales and factory personnel have the technical and enginering experience to help you select and design a cable tray system to meet your specific application requirments. This personal attention to your order continues every step of the way, including follow-up after delivery. Chalfant's large selection of cable tray products and accessories makes it easy to select the right solution for your cabling management applications. With industry leading advancements like our time saving TAB System and self-connecting wire mesh cable tray, Chalfant is always on the cutting edge, making cable managment more efficent.

Chalfant Manufacturing Company is active in NEMA's cable tray section - 5CT and a founding member of the Cable Tray Institute (CTI).

NEMA CTI Bicsi

Chalfant's Cable Tray and Products meet the following industry standards.

CLASSIFIED UL VDE CE CSA RoHS conform EMV EMC

Important: Chalfant reserves the right to CHANGE DESIGNS and/or CONFIGURATION of any product shown in this catalog.

www.chalfantcabletray.com
(330) 273-3510

Finishes

S

Electro Galvanized
Electro- Galvanized Steel to ASTM B 633

G

Hot Dipped
Hot Dipped Galvanized Steel after fabrication to ASTM A 123

T

Stainless Steel 304
304L Stainless Steel to ASTM A 380

Z

Stainless Steel 316
316L Stainless Steel to ASTM A 380

Painted
Electrostatic Painted Steel available in a variety of colors

A

Aluminum

P

Polyethylene
Polyethylene Temp resistance: hard types permanently up to about 90°C, briefly up to about 105°C. Soft types permanently up to about 80°C, briefly up to about 100°C and minus 40°C. Resistant to: alkalis and inorganic acids. Conditionally resistant to: acetone, organic acids, petrol, benzene, diesel oil, most oils. Not resistant to: chlorine, hydrocarbons, oxidizing acids.

Solutions for Industry Specific Applications



Wind Turbines- Turbines present challenges for routing cables safely down towers to base stations. Our wire mesh and ladder trays have been trusted by the industry leaders for years.



Sports Arenas- Growing demand for newer more fan friendly arenas have caused cities and towns across the country to upgrade their facilities. Our ladder and wire mesh trays install quickly making installtion down long corridors quick and easy.

Airports- Puntuality is crucial. All systems must work reliably with minimal downtime. The proper cable managment can make all the difference. Our cable tray systems protect cables while making access for upgrades easy.

Datacenters- High tech enviroments call for delicate cables such as fiber; our cable trays are designed to maintain proper bend radiuses and minimal deflections.

Oil and Gas- The harshest of enviroments call for the toughest of materials. Our extensive line of stainless steel products can stand up to the worst conditions.

Chalfant WM PG Rev 15-1

www.chalfantcabletray.com
(330) 273-3510

Industry- Miles of cables and long spans are amoung the list of challenges production facilities face when desiging their electrical infrastructure. Our line of NEMA rated ladders can support large loads over long spans

Marine- Our specially designed marine ladder and trays are perforated according to marine standards. Special finishes protect against corrosion and are pretreated for welding.

Office/Commercial- Office, retail and commercial spaces strive to be astethically pleasing. Our self connecting wire mesh tray requires no connection hardware making for seemless joints where ceilings are exposed.

Tunnels- Long spans and narrow passages require strong cable trays that can stand up to the elements. Our ladder trays and supports are designed for this very task. We also offer specially designed supports that work on curved ceilings and walls found in tunnel projects.



Solar- Whether you are mounting on a sloped roof, flat roof or on the ground. Our specially designed mounting solutions help to securely route critical cables along your solar installation.



1



Page 10

2

Page 20

3

Page 12

4

Page 15

5



Page 21

6

Page 17

7



Page 14



Chalfant WM PG Rev 15-1

www.chalfantcabletray.com
(330) 273-3510



Page 23

Page 16

Page 12



Page 21

Page 19



Page 13

Page 11

1” WIRE MESH TRAY



	Part Number	
Width	Finish S	Finish G
4”	WMGR104S	WMGR104G
6”	WMGR106S	WMGR106G
8”	WMGR108S	WMGR108G
12”	WMGR112S	WMGR112G

2” WIRE MESH TRAY



	Part Number			
Width	Finish S	Finish G	Finish T	Finish Z
2”	WMGR202S	WMGR202G	WMGR202T	WMGR202Z
4”	WMGR204S	WMGR204G	WMGR204T	WMGR204Z
6”	WMGR206S	WMGR206G	WMGR206T	WMGR206Z
8”	WMGR208S	WMGR208G	WMGR208T	WMGR208Z
12”	WMGR212S	WMGR212G	WMGR212T	WMGR212Z
18”	WMGR218S	WMGR218G	WMGR218T	WMGR218Z
24”	WMGR224S	WMGR224G	WMGR224T	WMGR224Z

4” WIRE MESH TRAY



	Part Number			
Width	Finish S	Finish G	Finish T	Finish Z
4”	WMGR404S	WMGR404G	WMGR404T	WMGR404Z
6”	WMGR406S	WMGR406G	WMGR406T	WMGR406Z
8”	WMGR408S	WMGR408G	WMGR408T	WMGR408Z
12”	WMGR412S	WMGR412G	WMGR412T	WMGR412Z
18”	WMGR418S	WMGR418G	WMGR418T	WMGR418Z
24”	WMGR424S	WMGR424G	WMGR424T	WMGR424Z

6” WIRE MESH TRAY

	Part Number	
Width	Finish S	Finish G
12”	WMST612S	WMST612G
18”	WMST618S	WMST618G
24”	WMST624S	WMST624G



Tee Bolts WMTB626 sold separately. (Page 3)

2” C- PROFILE WIRE MESH TRAY

	Part Number	
Width	Finish G	Finish T
2”	WMCP202G	WMCP202T
4”	WMCP204G	WMCP204T
8”	WMCP208G	WMCP208T
12”	WMCP212G	-
16”	WMCP216G	-



Tee Bolts WMTB626 sold separately. (Page 3)

COVERS

	Part Number		
Width	Finish S	Finish G	Finish T
2”	WM7S02118	WM7G02118	WM7T02118
4”	WM7S04118	WM7G04118	WM7T04118
6”	WM7S06118	WM7G06118	WM7T06118
8”	WM7S08118	WM7G08118	WM7T08118
12”	WM7S12118	WM7G12118	WM7T12118
18”	WM7S18118	WM7G18118	WM7T18118
24”	WM7S24118	WM7G24118	WM7T24118

COVER CLIP

Part Number	Finish	Pkg. Qty.	Ref Number
WM7CLAMPT	T	20	6065600

TEE BOLT ASSEMBLY

Part Number	Finish	Pkg. Qty.	Ref Number
WMTB620S	S	20	6016596
WMTB626S	S	20	6016589
WMTB620G	G	20	6016634
WMTB620T	T	20	6016642

For 6" Tray



Z Stainless Steel 316 available upon request

EXPANDING SPLICE CONNECTOR



Part Number	Finish	Pkg. Qty.	Ref Number
WMTB201S	S	100	6016715
WMTB201G	G	100	6016723
WMTB201T	T	100	6016731



Z Stainless Steel 316 available upon request

BOLT ASSEMBLY

Part Number	Finish	Pkg. Qty.	Ref Number
WMBC250S	S	20	6016855
WMBC250G	G	20	6016820
WMBC250T	T	20	6016839



Z Stainless Steel 316 available upon request

BARRIER STRIP CLAMP

Part Number	Finish	Pkg. Qty.	Ref Number
WMBSS	S	100	6017037
WMBSG	G	100	6017061
WMBST	T	100	6017045



Z Stainless Steel 316 available upon request

BONDING CLIP

Part Number	Finish	For Tray	Ref Number
WMGCLIPSM	S	2"- 6"	6016694
WMGCLIPLG	S	8"- 24"	6016696



GROUNDING LUGS



Part Number	Finish	Wire Size	Ref Number
WMGC-00	BRASS	8 STR.- 1/0 SER. CU	6404014
WMGC-01	BRASS	10 SOL.- 1 SER. CU	6404006

Mount to Bonding Clip
AWG Diameter:
10 AWG - 0.1019" (2.588mm)
8 AWG - 0.1285" (3.264mm)
1 AWG - 0.2893" (7.348mm)
1/0 AWG - 0.3249" (8.25mm)

REINFORCING SPLICE BAR



Part Number	Finish	Length	Ref Number
WMREMFKIT	G	10.5"(KIT)	1466500K

Kit Includes: (1) Bar, (4) Bolt Assemblies

90° SPLICE BRACKET



Part Number	Finish	Length	Ref Number
WM90BKG	G	9x9"(KIT)	6017371K

Kit Includes: (1) Bar (4) Bolt Assemblies (2) Hold Down Plates (1) Bolt and Nut

ASSEMBLY ANGLE 45°



Part Number	Finish	Pkg. Qty.	Ref Number
WM45ASMG	G	2	6017320
WM45ASMT	T	2	6017339

ASSEMBLY ANGLE 90°



	Part Number	Finish	Pkg. Qty.	Ref Number
(170mm) 6.69"	**WM90ASM1G**	G	2	6017347
(230mm) 9.05"	**WM90ASM2G**	G	2	6017355
(170mm) 6.69"	**WM90ASM1T**	T	2	6016278
(230mm) 9.05"	**WM90ASM2T**	T	2	6016308



C- TAB BRACKET

TAB SYSTEM

Part Number	Finish	Tray Width	Ref Number
WMTSC04	S	4”	6365906
WMTSC06	S	6”	6365914
WMTSC08	S	8”	6365922
WMTSC12	S	12”	6365949



End caps sold separately. (page 15)

L- TAB BRACKET

TAB SYSTEM

Part Number	Finish	Tray Width	Ref Number
WMTSL04	S	4”	6366015
WMTSL06	S	6”	6366023
WMTSL08	S	8”	6366031
WMTSL12	S	12”	6366066



End caps sold separately. (page 15)

C- BRACKET

Part Number	Finish	Tray Width	Ref Number
WMCBKT04	S	4”	6363806
WMCBKT08	S	8”	6363814
WMCBKT12	S	12”	6363822



Mounting hardware sold separately. (page 12)

End caps sold separately. (page 15)

L- BRACKET

Part Number	Finish	Tray Width	Ref Number
WMLBKT04	S	4”	6364101
WMLBKT06	S	6”	6364152
WMLBKT08	S	8”	6364209
WMLBKT12	S	12”	6364306



Mounting hardware sold separately. (page 12)

End caps sold separately. (page 15)

BRACKET EXTENDER



Part Number	Finish	Length	Ref Number
WMEBKT18	S	17.5”	6364322
WMEBKT22	S	21.5”	6364349
WMEBKT26	S	25.5”	6364365

End caps sold separately. (page 15)

SPACER



Part Number	Finish	Pkg. Qty.	Ref Number
WMSPACERS	S	20	6416551
WMSPACERG	G	20	6416586

END CAP



Part Number	Finish	Pkg. Qty.	Ref Number
WMENDCAP	P	10	6364625

WALL BRACKET



Part Number	Finish	Length	Ref Number
WM04322	G	4”	6420909
WM06322	G	6”	6420912
WM08322	G	8”	6420915
WM12322	G	12”	6420918
WM18322	G	18”	6420924
WM24322	G	24”	6420927

Mounting hardware sold separately. (page 12) or (page 18)

LIGHT DUTY WALL BRACKET

Part Number	Finish	Length	Ref Number
WM04300	S	4”	6424600
WM08300	S	8”	6424608
WM12300	S	12”	6424616



TAB PROFILE BRACKET

TAB SYSTEM

CENTER HANG

Part Number	Finish	For Tray	Ref Number
WM06263	S	6”	6366094
WM08263	S	8”	6366095
WM12263	S	12”	6366097
WM18263	S	18”	6366098
WM24263	S	24”	6366101



Hardware included: 2 nuts (3/8” or 1/2”)

TRAPEZE

Part Number	Finish	For Tray	Ref Number
WM04323	S	4”	6366095
WM06323	S	6”	6366096
WM08323	S	8”	6366097
WM12323	S	12”	6366098
WM18323	S	18”	6366100
WM24323	S	24”	6366102



Hardware included: 4 nuts (3/8” or 1/2”)

Holes support up to 1/2” threaded rod.

SUPPORT PLATE KIT



Part Number	Finish	Pkg. Qty.	Ref Number	Hole Diameter
WM38KIT	S	10	-	3/8"
WM12KIT	S	10	-	1/2"

Threaded rod sold separately.

HORIZONTAL BEAM SUPPORT



Part Number	Finish	Tray Width	Ref Number
WMHBS4G	G	4-6”	6003884
WMHBS8G	G	8”	6003892
WMHBS4T	T	4-6”	6003873
WMHBS8T	T	8”	6003879

Mount tray using (1) hold down clamp sold separately. (page 18)

VERTICAL BEAM SUPPORT



Part Number	Finish	Tray Width	Ref Number
WMVBS4G	G	4-6”	6003880
WMVBS8G	G	8”	6003888
WMVBS4T	T	4-6”	6003871
WMVBS8T	T	8”	6003877

Mount tray using (1) hold down clamp sold separately. (page 18)

SIDE HANGER



Part Number	Finish	Pkg. Qty.	Ref Number
WMSH249S	S	50	6015336
WMSH249G	G	50	6015338
WMSH249T	T	50	6015340

Z Stainless Steel 316 available upon request

Supports a 3/8” threaded rod. Threaded rod and nuts sold separately

EASY MOUNT SIDE HANGER



Part Number	Finish	Pkg. Qty.	Ref Number
WMSHEMS	S	1	6015322

HOLD DOWN CLAMP

Part Number	Finish	Diameter	Ref Number
WMHDC14S	S	1/4”	6015263
WMHDC38S	S	3/8”	6015276
WMHDC14G	G	1/4”	6015271
WMHDC38G	G	3/8”	6015278
WMHDC38T	T	3/8”	6015280

Package Qty. 50



SNAP IN WALL HANGER

Part Number	Finish	Pkg. Qty.	Ref Number
WMSWHS	S	1	6016443



JUNCTION BOX MOUNT

Part Number	Finish	Pkg. Qty.	Ref Number
WMJBMOUNT	G	1	7084773

Supports up to a 4.5” Junction Box

WALL TERMINATION BRACKET

Part Number	Finish	Length	Ref Number
WM04WT	G	4”	6373070-4
WM06WT	G	6”	6373070-6
WM08WT	G	8”	6373070-8
WM12WT	G	12”	6373070-12
WM18WT	G	18”	6373070-18
WM20WT	G	20”	6373070-20
WM24WT	G	24”	6373070-24



STANDOFF BRACKET



Part Number	Finish	Length	Ref Number
WM04FS	S	4”	6015654
WM06FS	S	6”	6015658
WM08FS	S	8”	6015662
WM12FS	S	12”	6015670
WM18FS	S	18”	6015689
WM24SF	S	24”	6015697

Standoff bracket height is 0.8”

GMA / (1/4 - 3/8)



	Part Number	Finish	Pkg. Qty.	Ref Number
1/4"	WMGMA14S	S	25	6015220
5/16"	WMGMA516S	S	25	6015239
3/8"	WMGMA38S	S	25	6015247
3/8"	WMGMA38G	G	25	6015255



For 4 and 6 inch wide tray only.

BEAM CLAMP



Part Number	Finish	Use With	Ref Number
WMBC20	G	US5	6003850
WMBC30	G	US7	6003869

MOUNTING BASE



Part Number	Finish	Tray Height	Ref Number
WMMOUNT65G	G	2”	6006486
WMMOUNT90G	G	4”	6006487
WMMOUNT65T	T	2”	6006488
WMMOUNT90T	T	4”	6006489

Box Qty. 1

END DROP OUT

Part Number	Finish	Length
WMCD04	A	4”
WMCD06	A	6”
WMCD08	A	8”
WMCD12	A	12”
WMCD18	A	18”
WMCD24	A	24”

Hardware included



SIDE DROP OUT

Part Number	Finish	Pkg. Qty.	Ref Number
WMCDSM	S	1	6220139
WMCDSMG	G	1	6220142



CONDUIT ADAPTOR

Part Number	Finish	Hole Size	Ref Number
WMCA12S	S	0.787”	6015425
WMCA34S	S	1.025 / 1.032	6015438
WMCA114S	S	1.734”	6015436
WMCA112S	S	1.984”	6015437

WMCA34S features a dual size knockout opening
Mounting hardware included



STRUT CLIP

Part Number	Finish	Pkg. Qty.	Ref Number
WMSHC	T	1	6016665



PLASTIC J HOOKS



	Part Number	Finish	Pkg. Qty.	Ref Number
1”	WMJHP-15	P	50	2205398
2”	WMJHP-30	P	50	2205404
3”	WMJHP-40	P	25	2205416

Use (1) WMBSS (sold separately, Page 12) to mount on cable tray

Self Connecting

color- light gray

METAL J HOOKS

	Part Number	Finish	Pkg. Qty.	Ref Number
1”	WMJHM-15	EG	50	2207028
2”	WMJHM-30	EG	25	2207036
3”	WMJHM-40	EG	10	2207060

Use (1) WMBSS (sold separately, Page 12) to mount on cable tray

END PLATE



Part Number	Finish	Tray Height	Tray Width	Ref Number
WMEPKIT04-2	S	2”	4,6,8,12”	7108004
WMEPKIT16-2	S	2”	16,20,24”	7108006
WMEPKIT18-2	S	2”	18”	7108008
WMEPKIT04-4	S	4”	4,6,8,12”	7108014
WMEPKIT16-4	S	4”	16,20,24”	7108016
WMEPKIT18-4	S	4”	18”	7108028

Includes (2) WMBSS for mounting on cable tray

RADIUS BEND



Part Number	Finish	Tray Height	Ref Number
WMRBKIT-2	S	2”	6220170
WMRBKIT-4	S	4”	6001892
WMRBKIT-6	S	6”	6220180



INDENTIFICATION PLATE

Part Number	Color	Pkg. Qty.	Ref Number
WMIDLG	Light Gray	10	6017710
WMIDDG	Dark Gray	10	6017711
WMIDOR	Orange	10	6017712
WMIDYE	Yellow	10	6017713
WMIDBL	Blue	10	6017714
WMIDGR	Green	10	6017715

Light Gray and Dark Gray labels are in printed with VA 1.4301 and VA 1.4571

Orange, Yellow, Blue and Green are blank

RUBBER END CAP

Part Number	Pkg. Qty.	Use With	Ref Number
WMREC-3.9	500	2-4" H 2-6" W	6003750
WMREC-4.8	500	2-4" H 8-24" W	6003754
WMREC-6.0	500	6" H 12-24" W	6003758



1” - BARRIER STRIP



Part Number	Finish	Tray Height	Ref Number
WMBS118-1S	S	1”	6062050
WMBS118-1G	G	1”	6062314
WMBS118-1T	T	1”	6062052

Z Stainless Steel 316 available upon request

Mount to tray using (3) Barrier Strip Clamps or Mounting Clips sold separately. (page 24)

2” - BARRIER STRIP



Part Number	Finish	Tray Height	Ref Number
WMBS118-2S	S	2”	6062033
WMBS118-2G	G	2”	6062321
WMBS118-2T	T	2”	6062025

Z Stainless Steel 316 available upon request

Mount to tray using (3) Barrier Strip Clamps or Mounting Clips sold separately. (page 24)

4” - BARRIER STRIP



Part Number	Finish	Tray Height	Ref Number
WMBS118-4S	S	4”	6062114
WMBS118-4G	G	4”	6062331
WMBS118-4T	T	4”	6062173

Z Stainless Steel 316 available upon request

Mount to tray using (3) Barrier Strip Clamps or Mounting Clips sold separately. (page 24)

6” - BARRIER STRIP



Part Number	Finish	Tray Height	Ref Number
WMBS118-6S	S	6”	6062122
WMBS118-6G	G	6”	6062335

Z Stainless Steel 316 available upon request

6” Barrier Strip nominal height is 4.33”

Mount to tray using (3) Barrier Strip Clamps or Mounting Clips sold separately. (page 24)

BARRIER STRIP CONNECTOR

Part Number	Finish	Pkg. Qty.	Ref Number
WMBSC-T	T	10	6067970

Barrier Strip Connector works with all sizes and finishes

BARRIER STRIP MOUNTING CLIP

Part Number	Finish	Pkg. Qty.	Ref Number
WMBSM-T	T	30	6062282

Barrier Strip Mounting Clip works with all sizes and finishes



BARRIER STRIP CLAMP

Part Number	Finish	Pkg.Qty.	Ref Number
WMBSS	S	100	6017037
WMBSG	G	100	6017061
WMBST	T	100	6017045

Z Stainless Steel 316 available upon request



UNDERFLOOR SUPPORT CLAMP



Part Number	Finish	Pkg. Qty.	Ref Number
WMUFSC	S	1	6406909

Clamp includes U bolt and truss head bolt for mounting Bracket



TAB BRACKET STAND



Part Number	Finish	Height	Ref Number
WM06TBS	S	6”	6015471
WM08TBS	S	8”	6015472
WM12TBS	S	12”	6015474

STANDOFF BRACKET



Part Number	Finish	Length	Ref Number
WM04FS	S	4”	6015654
WM06FS	S	6”	6015658
WM08FS	S	8”	6015662
WM12FS	S	12”	6015670
WM18FS	S	18”	6015689
WM24FS	S	24”	6015697

Standoff bracket height is 0.8”

UNDERFLOOR STAND



Part Number	Finish	Pkg. Qty.	Ref Number
WMUFS	S	1	6015478

Bracket height is 4”

GR-Magic Self Connecting Cable Tray







Large Radius 90 Degree Bend



Zero Radius 90 Degree Bend

















Chalfant WM PG Rev 15-1

Loose T and 4 Way Intersection















Elbow Bend




4” 100mm
1
1
1


6” 150mm
2
1
2


8” 200mm
2
2
2


12” 300mm
3
2
3


18” 450mm
4
2
4


20” 500mm
5
2
5


24” 600mm
6
2
6

Reduction Assembly









Installation Instructions

□ □□□ 4 □□□ □□□□□□□□□

















Vertical Dropout













Vertical Bend









Expansion Joint







Reinforcing Splice Bar
part number: WMREMFKIT

INSTALLATION INSTRUCTIONS

Cover Clips



Cover Clips
part number: WM7CLAMPT

Side Hanger







Side Hanger
part number: WMSH294

End Plate









Barrier Strip Clamp
part number: WMBSS

Grounding Lug





Grounding Lug
part number: WMGC-00 / 01

Barrier Strip



Barrier Strip
part number: WMBS118-xx

Barrier Strip Connector
part number: WMBSC-T

Strut Clip

Strut Clip
part number: WMSHC

Wire Mesh Tray 2”

Part Number	Tray Size		Number of Cables			
	inch	mm	Cat. 3	Cat. 5	Cat. 6	Cat. 6A
WMGR204	2x4	50x100	142	122	81	50
WMGR206	2x6	50x150	215	184	123	76
WMGR208	2x8	50x200	288	246	164	101
WMGR212	2x12	50x300	439	376	251	155
WMGR216	2x16	50x400	589	505	337	208
WMGR218	2x18	50x450	665	570	380	235
WMGR220	2x20	50x500	740	635	423	261
WMGR224	2x24	50x600	891	764	509	315

Wire Mesh Tray 4”

Part Number	Tray Size		Number of Cables			
	inch	mm	Cat. 3	Cat. 5	Cat. 6	Cat. 6A
WMGR404	4x4	100x100	296	256	169	104
WMGR406	4x6	100x150	451	386	258	159
WMGR408	4x8	100x200	605	519	346	214
WMGR412	4x12	100x300	923	791	527	326
WMGR416	4x16	100x400	1240	1063	709	438
WMGR418	4x18	100x450	1399	1199	800	494
WMGR420	4x20	100x500	1558	1335	890	550
WMGR424	4x24	100x600	1875	1608	1072	662

Wire Mesh Tray 6”

Part Number	Tray Size		Number of Cables			
	inch	mm	Cat. 3	Cat. 5	Cat. 6	Cat. 6A
WMST612	6x12	150x300	1407	1206	792	497
WMST618	6x18	150x450	2133	1829	1204	753
WMST620	6x20	150x500	2375	2036	1341	838
WMST624	6x24	150x600	2860	2451	1616	1009

Fill rates are applicable to all tray finishes for the listed size.

Fill rates are based on a 50% fill capacity as per NEC standards. Some industry standards require a 40% fill rate. Category 3 cables are based on a 0.175 diameter, Category 5 cables are based on a 0.188 diameter, Category 6 cables are based on a 0.233 diameter, Category 6A cables are based on a 0.295 diameter.

Installation of any of the displaced or listed products should be performed only by properly qualified and trained personnel in compliance with all applicable national, state and local electrical standards, building codes, and other laws and regulations. Proper installation and product selection must take into consideration conditions and materials at the installation site, environmental conditions, manufacturer established parameters for the use of the relevant product. The buyer and installer are responsible for selecting the appropriate product for their application. Failure to comply with the manufacturer instructions or usage parameters, including cutting or modifying any of the products, may result in reduced product life or product failure, potentially resulting in damage to person and property, and will void any manufacturer warranty or approvals, certifications, listings which the product was designed and tested for. © 2014 Chalfant Manufacturing Company

Part Number	Page
WM04300	16
WM04322	15
WM04323	16
WM04FS	19
WM04FS	25
WM04WT	18
WM06263	16
WM06322	15
WM06323	16
WM06FS	19
WM06FS	25
WM06TBS	25
WM06WT	18
WM08263	16
WM08300	16
WM08322	15
WM08323	16
WM08FS	19
WM08FS	25
WM08TBS	25
WM08WT	18
WM12263	16
WM12300	16
WM12322	15
WM12323	16
WM12FS	19
WM12FS	25
WM12KIT	16
WM12TBS	25
WM12WT	18
WM18263	16
WM18322	15
WM18323	16
WM18FS	19
WM18FS	25
WM20WT	18
WM24263	16
WM24322	15
WM24323	16
WM24FS	25
WM24SF	19
WM24WT	18
WM38KIT	16
WM45ASMG	13
WM45ASMT	13
WM7CLAMPT	11
WM7G02118	11
WM7G04118	11
WM7G06118	11

Part Number	Page
WM7G08118	11
WM7G12118	11
WM7G18118	11
WM7G24118	11
WM7S02118	11
WM7S04118	11
WM7S06118	11
WM7S08118	11
WM7S12118	11
WM7S18118	11
WM7S24118	11
WM7T02118	11
WM7T04118	11
WM7T06118	11
WM7T08118	11
WM7T12118	11
WM7T18118	11
WM7T24118	11
WM90ASM1G	13
WM90ASM1T	13
WM90ASM2G	13
WM90ASM2T	13
WM90BKG	13
WMBC20	19
WMBC250G	12
WMBC250S	12
WMBC250T	12
WMBC30	19
WMBS118-1G	23
WMBS118-1S	23
WMBS118-1T	23
WMBS118-2G	23
WMBS118-2S	23
WMBS118-2T	23
WMBS118-4G	23
WMBS118-4S	23
WMBS118-4T	23
WMBS118-6G	23
WMBS118-6S	23
WMBSC-T	24
WMBSG	12
WMBSG	24
WMBSM-T	24
WMBSS	12
WMBSS	24
WMBST	12
WMBST	24
WMCA112S	20
WMCA114S	20

Part Number	Page
WMCA12S	20
WMCA34S	20
WMCBKT04	14
WMCBKT08	14
WMCBKT12	14
WMCD04	20
WMCD06	20
WMCD08	20
WMCD12	20
WMCD18	20
WMCD24	20
WMCDSM	20
WMCDSMG	20
WMCP202G	11
WMCP202T	11
WMCP204G	11
WMCP204T	11
WMCP208G	11
WMCP208T	11
WMCP212G	11
WMCP216G	11
WMEBKT18	15
WMEBKT22	15
WMEBKT26	15
WMENDCAP	15
WMEPKIT04-2	21
WMEPKIT04-4	21
WMEPKIT16-2	21
WMEPKIT16-4	21
WMEPKIT18-2	21
WMEPKIT18-4	21
WMGC-00	13
WMGC-01	13
WMGCLIPLG	12
WMGCLIPSM	12
WMGMA14S	19
WMGMA38G	19
WMGMA38S	19
WMGMA516S	19
WMGR104G	10
WMGR104S	10
WMGR106G	10
WMGR106S	10
WMGR108G	10
WMGR108S	10
WMGR112G	10
WMGR112S	10
WMGR202G	10
WMGR202S	10

Part Number	Page
WMGR202T	10
WMGR202Z	10
WMGR204G	10
WMGR204S	10
WMGR204T	10
WMGR204Z	10
WMGR206G	10
WMGR206S	10
WMGR206T	10
WMGR206Z	10
WMGR208G	10
WMGR208S	10
WMGR208T	10
WMGR208Z	10
WMGR212G	10
WMGR212S	10
WMGR212T	10
WMGR212Z	10
WMGR218G	10
WMGR218S	10
WMGR218T	10
WMGR218Z	10
WMGR224G	10
WMGR224S	10
WMGR224T	10
WMGR224Z	10
WMGR404G	10
WMGR404S	10
WMGR404T	10
WMGR404Z	10
WMGR406G	10
WMGR406S	10
WMGR406T	10
WMGR406Z	10
WMGR408G	10
WMGR408S	10
WMGR408T	10
WMGR408Z	10
WMGR412G	10
WMGR412S	10
WMGR412T	10
WMGR412Z	10
WMGR418G	10
WMGR418S	10
WMGR418T	10
WMGR418Z	10
WMGR424G	10
WMGR424S	10
WMGR424T	10

Part Number	Page
WMGR424Z	10
WMHBS4G	17
WMHBS4T	17
WMHBS8G	17
WMHBS8T	17
WMHDC14G	18
WMHDC14S	18
WMHDC38G	18
WMHDC38S	18
WMHDC38T	18
WMIDBL	22
WMIDDG	22
WMIDGR	22
WMIDLG	22
WMIDOR	22
WMIDYE	22
WMJBMOUNT	18
WMJHM-15	21
WMJHM-30	21
WMJHM-40	21
WMJHP-15	21
WMJHP-30	21
WMJHP-40	21
WMLBKT04	14
WMLBKT06	14
WMLBKT08	14
WMLBKT12	14
WMMOUNT65G	19
WMMOUNT65T	19
WMMOUNT90G	19
WMMOUNT90T	19
WMRBKIT-2	21
WMRBKIT-4	21
WMRBKIT-6	21
WMREC-3.9	22
WMREC-4.8	22
WMREC-6.0	22
WMREMFKIT	13
WMSH249G	17
WMSH249S	17
WMSH249T	17
WMSHC	20
WMSHEMS	17
WMSPACERG	15
WMSPACERS	15
WMST612G	11
WMST612S	11
WMST618G	11
WMST618S	11

Part Number	Page
WMST624G	11
WMST624S	11
WMSWHS	18
WMTB201G	12
WMTB201S	12
WMTB201T	12
WMTB620G	12
WMTB620S	12
WMTB620T	12
WMTB626S	12
WMTSC04	14
WMTSC06	14
WMTSC08	14
WMTSC12	14
WMTSL04	14
WMTSL06	14
WMTSL08	14
WMTSL12	14
WMUFS	25
WMUFSC	25
WMVBS4G	17
WMVBS4T	17
WMVBS8G	17
WMVBS8T	17









Chalfant's additional tray offerings include Ladder Tray, Series 6, Series 5, Ventilated, AZ Channel lines, Shielded and Com-Tray. With over 70 years experience manufacturing and pioneering cable tray design Chalfant Manufacturing Company has the products and experience to help you select the right cable tray system for your project and deliver exceptional products and service from design to completion.
Visit www.chalfantcabletray.com for additional information and a complete listing of our cable tray products.

Ladder Tray

- Over 28 models to choose from including aluminum, galvanized and stainless steel
- Manufactured to NEMA specifications
- UL listed
- Complete line of bends, risers, tee's and accessories

Series 6

- Solid or louvered openings
- Meets NEC Article 392-5
- Manufactured to NEMA specifications
- UL listed
- Complete line of bends, risers, tee's and accessories

Ventiliated Cable Tray

- Choose from ventilated or solid in heights from 1- 4" and widths from 2-24"
- Available in strip galvanized, hot-dip galvanized and stainless steel
- UL listed
- Complete line of bends, risers, tee's and accessories

AZ Channel

- Perfect for automation and control system applications requiring frequent drop outs.
- Various hole sizes make routing pre-connectorized cables easy
- UL listed
- Available in strip galvanized, hot-dip galvanized and stainless steel

Chalfant WM PG Rev 15-1

www.chalfantcabletray.com
Phone: (330) 273-3510