


## Central hanger for cable tray, side height 60

Central suspension for cable trays with rolled side rail of side height 60 mm. The central suspension possesses a rotatable M10 threaded sleeve. When filling, ensure an even distribution of the load (avoid one-sided filling).



Type	For width mm	For threaded rod	Dimension B mm	Dimension b mm	F in kN	Pack. pcs	Weight kg/100 pcs.	Item No.
MAH 60 100 FS	100	M10	94	84	0,9	20	18,500	6358705
MAH 60 150 FS	150	M10	144	134	0,65	20	23,000	6358709
MAH 60 200 FS	200	M10	195	184	0,45	20	27,600	6358713
MAH 60 300 FS	300	M10	295	284	0,22	20	36,700	6358717
MAH 60 400 FS	400	M10	395	384	–	20	46,000	6358720
MAH 60 100 FT	100	M10	94	84	0,9	20	18,500	6358752
MAH 60 150 FT	150	M10	144	134	0,65	20	23,000	6358756
MAH 60 200 FT	200	M10	195	184	0,45	20	27,600	6358760
MAH 60 300 FT	300	M10	295	284	0,22	20	36,700	6358764

**St** Steel

**FS** Strip-galvanised

**FT** Hot-dip galvanised

### Dimensions

